

**Deadend, Straight line, Swing Away,
Side Open, 336.4 19 STR to 954 61
STR AL, 300 26/7 to 954 36/1
ACSR, Fitting: NONE**

By FARGO
Catalog # [GD967A](#)



*Representative Image

Deadend, Straight line, Swing Away, Side Opening, 336.4 19 STR to 954 61 STR AL, 300 26/7 to 954 36/1 ACSR, Conductor Range 0.68 - 1.15 in, Fitting: NONE

Features

- For distribution and light transmission construction.
- The pressure pad is easily lifted and swung clear of the cable groove permitting convenient top loading of the conductor without disassembly.
- The large pulling eye makes it convenient to connect and disconnect the “come-along” hook.

General

Catalog Number	GD967A
EU RoHS Indicator	Contact Manufacturer
Fitting Type	NONE
Material	Aluminum
Material - Body	356 T6 Aluminum Alloy
Material - Hardware	Galvanized Steel
Material - Keeper	356 T6 Aluminum Alloy
Product Category	Straight Line
Strength Rating - Ultimate	10000 lb
Body	
Style	GD900
Type	Bolted
UPC	096359309758

Dimensions

Clevis Opening	1.25 in
Diameter - Bolt	0.5 in
Diameter - Pin	0.625 in
Weight	3.72 lb

Electrical Ratings

Voltage Application	Standard
---------------------	----------

Conductor Related

Conductor Compatibility	ACSR-Ostrich-300-26/7;ACSR-Merlin-336.4-18/1;ACSR-Linnet-336.4-26/7;ACSR-Oriole-336.4-30/7;ACSR-Chickadee-397.5-18/1;ACSR-Brant-397.5-
-------------------------	--

24/7;ACSR-Ibis-397.5-26/7;ACSR-Lark-397.5-30/7;ACSR-Pelican-477-18/1;ACSR-Flicker-477-24/7;ACSR-Hawk-477-26/7;ACSR-Hen-477-30/7;ACSR-Osprey-556.5-18/1;ACSR-Parakeet-556.5-24/7;ACSR-Dove-556.5-26/7;ACSR-Eagle-556.5-30/7;ACSR-Peacock-605-24/7;ACSR-Squab-605-26/7;ACSR-Teal-605-30/19;ACSR-Kingbird-636-18/1;ACSR-Swift-636-36/1;ACSR-Rook-636-24/7;ACSR-Grosbeak-636-26/7;ACSR-Egret-636-30/19;ACSR-Flamingo-666.6-24/7;ACSR-Gannet-666.6-26/7;ACSR-Stilt-715.5-24/7;ACSR-Starling-715.5-26/7;ACSR-Redwing-715.5-30/19;ACSR-Coot-795-36/1;ACSR-Cuckoo-795-24/7;ACSR-Drake-795-26/7;ACSR-Tern-795-45/7;ACSR-Condor-795-54/7;ACSR-Mallard-795-30/19;ACSR-Ruddy-900-45/7;ACSR-Brahma-203.2-16/19;AAC-Canna-397.5-19;AAC-Cosmos-477-19;AAC-Syringa-477-37;AAC-Zinnia-500-19;AAC-Hyacinth-500-37;AAC-Dahlia-556.5-19;AAC-Mistletoe-556.5-37;AAC-Meadowsweet-600-37;AAC-Orchid-636-37;AAC-Flag-700-61;AAC-Violet-715.5-37;AAC-Nasturtium-715.5-61;AAC-

	Cattail-750-61;AAC-Arbutus-795-37;AAC-Lilac-795-61;AAC-Cockscomb-900-37;AAC-Snapdragon-900-61;AAC-Magnolia-954-37;AAC-Goldenrod-954-61;ACAR-653.1-12/7;ACAR-739.8-18/19;ACAR-853.7-30/7
Conductor Diameter - Maximum	1.15
Conductor Diameter - Minimum	0.68
Conductor Diameter Range	0.68 - 1.15

Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2024)
--------------------------	---

Logistics

Pallet Quantity	320
-----------------	-----

Product Assets

- Catalogs - Distribution Connectors
- Literature - Ropes Course Industry Letter (April 2021)
- Specifications - GD967A