

Automatic Guy Wire Deadend, 1/4" 7 Strand, EHS

By FARGO
Catalog # [GDE5100](#)



Automatic Guy Wire Deadend, 1/4" 7 Strand, HS, EHS,
Common, Siemens-Martin, Utilities and Bell System Strand

*Representative Image

General

Bail Option	Standard
Material	Aluminum Alloy; Steel
Material - Bail	Stainless Steel
Material - Jaw	HS Plated Steel
Material - Shell	High Strength Aluminum Alloy
Material - Yoke	Aluminum Alloy
Product Category	Guy Wire
Type	Automatic
UPC	096359363446

Dimensions

Assembly Rating (Ultimate)	6700 lb
Length	9.200 in
Nominal Guy Wire Size	1/4" 7 Strand
Weight	0.331 lb
Width	1.40 in

Conductor Related

Conductor Diameter - Maximum	0.253
Conductor Diameter - Minimum	0.24
Conductor Diameter Range	0.24 - 0.253

Logistics

Pallet Quantity	3600
-----------------	------

Product Assets

[Catalogs - Communications Catalog \(CA12042E\)](#)
[Catalogs - Communication Connectors - Deadends and Splices](#)
[Catalogs - Distribution Connectors \(CA05127E\)](#)
[Literature - Ropes Course Industry Letter \(April 2021\)](#)
[Sales Drawings - GDE520x Sales Drawing](#)
[Sales Drawings - GDE51xx Sales Drawing](#)

Related Products

[GDE5200L - Automatic Guy Wire Deadend, 1/4", EHS Long Bail](#)
[GDE5200 - Automatic Guy Wire Deadend, 1/4" EHS](#)
[GDE5100L - Automatic Guy Wire Deadend, 1/4" 7 Strand, EHS, Long Bail](#)