

Automatic Guy Wire Deadend, 3/8" 7 Strand

By FARGO
Catalog # [GDE5102](#)

Automatic Guy Wire Deadend, 3/8" 7 Strand, HS, Common,
Siemens-Martin, Utilities and Bell System Strand



*Representative Image

Features

- Fargo GDE5100 Series Automatic deadends offer the quickest means of deadending guy strand.
- Use suffix "L" for long bail.

General

Bail Option	Standard
Catalog Number	GDE5102
Material	Aluminum Alloy; Steel
Material - Bail	Stainless Steel
Material - Jaw	HS Plated Steel
Material - Shell	High Strength Aluminum Alloy
Material - Yoke	Aluminum Alloy
Product Category	Guy Wire
Type	Automatic
UPC	096359363101

Dimensions

Assembly Rating (Ultimate)	11500 lb
Length	11.5 in
Nominal Guy Wire Size	3/8" 7 Strand
Thickness - Pad	0 in
Weight	1.058 lb

Width	2 in
-------	------

Conductor Related

Conductor Diameter - Maximum	0.405
Conductor Diameter - Minimum	0.36
Conductor Diameter Range	0.36 - 0.405

Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2025)
--------------------------	---

Logistics

Pallet Quantity	1600
-----------------	------

Product Assets

- [Catalogs - Distribution Connectors](#)
- [Catalogs - Communication Connectors - Deadends and Splices](#)
- [Catalogs - Communications Catalog](#)
- [Literature - Ropes Course Industry Letter \(April 2021\)](#)
- [Sales Drawings - GDE520x Sales Drawing](#)
- [Sales Drawings - GDE51xx Sales Drawing](#)
- [Specifications - GDE5102](#)