

Automatic Guy Wire Deadend, 1/4"
EHS

By FARGO
Catalog # [GDE5200](#)



*Representative Image

Features

- Fargo GDE5200 Series Automatic deadends are designed for use on all grades of galvanized steel wire strand ... High Strength, Extra High Strength, Alumoweld®, Aluminized, Common, Siemens-Martin, Utilities and Bell System Strand.
- Innovative yoke design allows for installation without use of a gripping hook
- Use suffix "L" for long bail

General

Bail Option	Standard
Catalog Number	GDE5200
Material	Aluminum Alloy; Steel
Material - Bail	Stainless Steel
Material - Jaw	HS Plated Steel
Material - Shell	High Strength Aluminum Alloy
Material - Yoke	Aluminum Alloy
Product Category	Guy Wire
Type	Automatic
UPC	096359373346

Dimensions

Length	10 in
Nominal Guy Wire Size	1/4" 7 Strand
Weight	0.591 lb
Width	2.7 in

Conductor Related

Conductor Diameter - Maximum	0.249
Conductor Diameter - Minimum	0.231
Conductor Diameter Range	0.231 - 0.249

Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2024)
--------------------------	---

Logistics

Carton Quantity	50
Pallet Quantity	2400

Product Assets

- [Catalogs - Distribution Connectors](#)
- [Catalogs - Communication Connectors - Deadends and Splices](#)
- [Catalogs - Communications Catalog](#)
- [Installation Manuals - GDE52xx Guy Wire Automatic Deadends - installation instructions](#)
- [Literature - Ropes Course Industry Letter \(April 2021\)](#)
- [Sales Drawings - GDE520x Sales Drawing](#)
- [Sales Drawings - GDE51xx Sales Drawing](#)
- [Specifications - GDE5200](#)