

Automatic Guy Wire Deadend, 1/4", EHS Long Bail

By FARGO
Catalog # [GDE5200L](#)



Automatic Guy Wire Deadend, 1/4", HSS, EHS, Common, Siemens-Martin, Utilities and Bell System Strand, Long Bail

*Representative Image

Features

- Long Bail.

General

Bail Option	Long
EU RoHS Indicator	Contact Manufacturer
Material	Aluminum Alloy; Steel
Material - Bail	Stainless Steel
Material - Jaw	HS Plated Steel
Material - Shell	High Strength Aluminum Alloy
Material - Yoke	Aluminum Alloy
Product Category	Guy Wire
Type	Automatic
UPC	096359375364

Dimensions

Assembly Rating (Ultimate)	6700 lb
Diameter - Clamping Hardware	0 in
Nominal Guy Wire Size	1/4" 7 Strand
Weight	0.350 lb

Conductor Related

Clamping Range	0- 0
Conductor Diameter - Maximum	0.27
Conductor Diameter - Minimum	0.215
Conductor Diameter Range	0.215 - 0.27

Logistics

Pallet Quantity	1400
-----------------	------

Product Assets

[Catalogs - Communications Catalog \(CA12042E\)](#)
[Catalogs - Communication Connectors - Deadends and Splices](#)
[Catalogs - Distribution Connectors \(CA05127E\)](#)
[Installation Manuals - GDE52xx Guy Wire Automatic Deadends - installation instructions](#)
[Literature - Ropes Course Industry Letter \(April 2021\)](#)
[Sales Drawings - GDE520x Sales Drawing](#)
[Sales Drawings - GDE51xx Sales Drawing](#)

Related Products

[GDE5100 - Automatic Guy Wire Deadend, 1/4" 7 Strand, EHS](#)
[GDE5100L - Automatic Guy Wire Deadend, 1/4" 7 Strand, EHS, Long Bail](#)
[GDE5200 - Automatic Guy Wire Deadend, 1/4" EHS](#)