

# Automatic Guy Wire Deadend, 5/16" EHS

By FARGO  
Catalog # [GDE5201](#)



Automatic Guy Wire Deadend, 5/16", HSS, EHS, Common,  
Siemens-Martin, Utilities and Bell System Strand

\*Representative Image

## Features

- Fargo GDE5200 Series Automatic deadends are designed for use on all grades of galvanized steel wire strand ... High Strength, Extra High Strength, Alumoweld®, Aluminized, Common, Siemens-Martin, Utilities and Bell System Strand.
- Innovative yoke design allows for installation without use of a gripping hook
- Use suffix "L" for long bail

## General

Bail Option	Standard
Material	Aluminum Alloy; Steel
Material - Bail	Stainless Steel
Material - Jaw	HS Plated Steel
Material - Shell	High Strength Aluminum Alloy
Material - Yoke	Aluminum Alloy
Product Category	Guy Wire
Type	Automatic
UPC	096359373353

## Dimensions

Length	10.000 in
Nominal Guy Wire Size	5/16" 7 Strand
Weight	.0941 lb
Width	2.800 in

## Conductor Related

Conductor Diameter - Maximum	0.324
Conductor Diameter - Minimum	0.261
Conductor Diameter Range	0.261 - 0.324

## Logistics

Pallet Quantity	2400
-----------------	------

## Product Assets

[Catalogs - Communications Catalog \(CA12042E\)](#)  
[Catalogs - Communication Connectors - Deadends and Splices](#)  
[Catalogs - Distribution Connectors \(CA05127E\)](#)  
[Installation Manuals - GDE52xx Guy Wire Automatic Deadends - installation instructions](#)  
[Literature - Ropes Course Industry Letter \(April 2021\)](#)  
[Sales Drawings - GDE520x Sales Drawing](#)  
[Sales Drawings - GDE51xx Sales Drawing](#)

## Related Products

[GDE5101L - Automatic Guy Wire Deadend, 5/16" 7 Strand, HS, Long Bail](#)  
[GDE5101 - Automatic Guy Wire Deadend, 5/16" 7 Strand](#)  
[GDE5201L - Automatic Guy Wire Deadend, 5/16", EHS, Long Bail](#)