

HUBBELL

Power Systems

Automatic Guy Wire Deadend, 5/16", EHS, Long Bail

By FARGO
Catalog # [GDE5201L](#)



Automatic Guy Wire Deadend, 5/16", HSS, EHS, Common,
Siemens-Martin, Utilities and Bell System Strand, Long Bail

*Representative Image

Features

Long Bail.

General

Bail Option	Long
Bolt Installation Torque (Recommended)	0 ft-lbs
Catalog Number	GDE5201L
Material	Aluminum Alloy; Steel
Material - Bail	Stainless Steel
Material - Jaw	HS Plated Steel
Material - Shell	High Strength Aluminum Alloy
Material - Yoke	Aluminum Alloy
Number of Pad Holes	0
Product Category	Guy Wire
Type	Automatic
UPC	096359375371

Dimensions

Actual Clamp Strand Diameter Range	0 in
Adjustment Step	0 in
Angle - Pad	0 °
Assembly Rating (Ultimate)	11200 lb
Clamping - Maximum	0 in
Clamping - Minimum	0 in
Diameter - Clamping Hardware	0 in
Diameter - Clevis Pin	0 in
Diameter - Eye Hole	0 in
Diameter - Inside	0 in
Diameter - Pad Bolt	0 in
Length	15.3 in
Length - Pin	0 in
Nominal Guy Wire Size	5/16" 7 Strand
Take Up	0 in
Thickness - Pad	0 in
Total Adjustment	0 in
Weight	.0941 lb
Width	2.8 in

Conductor Related

Clamping Range	0- 0
Conductor Diameter - Maximum	0.315
Conductor Diameter - Minimum	0.27
Conductor Diameter Range	0.27 - 0.315

Logistics

Pallet Quantity	1600
-----------------	------

Product Assets

[Catalogs - Communications Catalog](#)
[Catalogs - Distribution Connectors](#)
[Catalogs - Communication Connectors - Deadends and Splices](#)
[Installation Manuals - GDE52xx Guy Wire Automatic Deadends -
installation instructions](#)
[Literature - Ropes Course Industry Letter \(April 2021\)](#)
[Sales Drawings - GDE520x Sales Drawing](#)
[Sales Drawings - GDE51xx Sales Drawing](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
FG-GDE5201L-SPEC-EN | REV 6/2024