

HUBBELL

Power Systems

Automatic Guy Wire Deadend, 3/8" EHS

By FARGO
Catalog # [GDE5202](#)



Automatic Guy Wire Deadend, 3/8", HSS, EHS, Common,
Siemens-Martin, Utilities and Bell System Strand

*Representative Image

Features

- Fargo GDE5200 Series Automatic deadends are designed for use on all grades of galvanized steel wire strand ... High Strength, Extra High Strength, Alumoweld®, Alumonized, Common, Siemens-Martin, Utilities and Bell System Strand.
- Innovative yoke design allows for installation without use of a gripping hook
- Use suffix "L" for long bail

General

Bail Option	Standard
Catalog Number	GDE5202
Material	Aluminum Alloy; Steel
Material - Bail	Stainless Steel
Material - Jaw	HS Plated Steel
Material - Shell	High Strength Aluminum Alloy
Material - Yoke	Aluminum Alloy
Product Category	Guy Wire
Type	Automatic
UPC	096359374145

Dimensions

Length	11.8 in
Nominal Guy Wire Size	3/8" 7 Strand
Weight	1.42 lb
Width	3.5 in

Conductor Related

Conductor Diameter - Maximum	0.399
Conductor Diameter - Minimum	0.327
Conductor Diameter Range	0.327 - 0.399

Logistics

Pallet Quantity 1000

Product Assets

[Catalogs - Communications Catalog](#)
[Catalogs - Distribution Connectors](#)
[Catalogs - Communication Connectors - Deadends and Splices](#)
[Installation Manuals - GDE52xx Guy Wire Automatic Deadends - installation instructions](#)
[Literature - Ropes Course Industry Letter \(April 2021\)](#)
[Sales Drawings - GDE520x Sales Drawing](#)
[Sales Drawings - GDE51xx Sales Drawing](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
FG-GDE5202-SPEC-EN | REV 6/2024