


# HUBBELL

## Power Systems

### Stirrup, Extruded Type

By FARGO  
Catalog # [GH286AL](#)

Overhead Stirrup, Bolted, Stirrup, Extruded, Aluminum,  
AAC|AAAC|ACSR, Range 0.563 - 1.140 in



\*Representative Image

#### Features

Extruded shape develops vibration proof connection.

#### General

Bolt Installation Torque (Recommended)	300 in-lbs
Catalog Number	GH286AL
Hot Stick Eyes	Yes
Inhibitor Loaded	Yes
Material	Aluminum Alloy
Material - Bail	Copper
Material - Body	Aluminum Alloy
Material - Eystem	Aluminum Alloy
Material - Keeper	Aluminum Alloy
Material - Stirrup	Copper
Number of Hot Stick Eyes	1
Plating	No
Style	Extruded Aluminum
Type	Stirrups
UPC	096359310587

#### Dimensions

Copper Loop Size	0.625 in
Diameter - Bolt	0.5 in
Diameter - Stirrup Nominal Wire	2/0 Solid
Dimensions	4.375 in x 5.500 in x 6.500 in
Height	6.5 in
Length	4.375 in
Weight	1.32 lb
Width	5.5 in
Width - Main Contact	2.4375 in

## Conductor Related

Conductor Compatibility

ACSR-Sparrow-2-6/1;ACSR-Sparate-2-7/1;ACSR-Robin-1-6/1;ACSR-Raven-1/0-6/1;ACSR-Quail-2/0-6/1;ACSR-Pigeon-3/0-6/1;ACSR-Penguin-4/0-6/1;ACSR-Waxwing-266.8-18/1;ACSR-Partridge-266.8-26/7;ACSR-Ostrich-300-26/7;ACSR-Merlin-336.4-18/1;ACSR-Linnet-336.4-26/7;ACSR-Oriole-336.4-30/7;ACSR-Chickadee-397.5-18/1;ACSR-Brant-397.5-24/7;ACSR-Ibis-397.5-26/7;ACSR-Lark-397.5-30/7;ACSR-Pelican-477-18/1;ACSR-Flicker-477-24/7;ACSR-Hawk-477-26/7;ACSR-Hen-477-30/7;ACSR-Osprey-556.5-18/1;ACSR-Parakeet-556.5-24/7;ACSR-Dove-556.5-26/7;ACSR-Eagle-556.5-30/7;ACSR-Peacock-605-24/7;ACSR-Squab-605-26/7;ACSR-Teal-605-30/19;ACSR-Kingbird-636-18/1;ACSR-Swift-636-36/1;ACSR-Rook-636-24/7;ACSR-Grosbeak-636-26/7;ACSR-Egret-636-30/19;ACSR-Flamingo-666.6-24/7;ACSR-Gannet-666.6-26/7;ACSR-Stilt-715.5-24/7;ACSR-Starling-715.5-26/7;ACSR-Redwing-715.5-30/19;ACSR-Coot-795-36/1;ACSR-Tern-795-45/7;ACSR-Brahma-203.2-16/19;AAC-Iris-2-7;AAC-Pansy-1-7;AAC-Poppy-1/0-7;AAC-Aster-2/0-7;AAC-Phlox-3/0-7;AAC-Oxlip-4/0-7;AAC-Valerian-250-19;AAC-Laurel-266.8-19;AAC-Daffodil-350-19;AAC-Canna-397.5-19;AAC-Cosmos-477-19;AAC-Syringa-477-37;AAC-Zinnia-500-19;AAC-Hyacinth-500-37;AAC-Dahlia-556.5-19;AAC-Mistletoe-556.5-37;AAC-Meadowsweet-600-37;AAC-Orchid-636-37;AAC-Flag-700-61;AAC-Violet-715.5-37;AAC-Nasturtium-715.5-61;AAC-Cattail-750-61;AAC-Arbutus-795-37;AAC-Lilac-795-61;AAAC 6201 Alloy-Ames-77.47-6/18;AAAC 6201 Alloy-Azusa-123.3-6/18;AAAC 6201 Alloy-Anaheim-155.4-6/18;AAAC 6201 Alloy-Amherst-195.7-6/18;AAAC 6201 Alloy-Alliance-246.9-6/18

## Logistics

Packaging Type

Bag

Pallet Quantity

800

## Product Assets

[Catalogs - Distribution Connectors](#)

[Sales Drawings - CC-25764](#)

[Video - Hubbell Power Systems Hotline Tap Clamps and Stirrup Clamps](#)

[Video - Hubbell Power Systems In Depth: Stirrup Clamps](#)

Conductor Diameter - 1.14  
Maximum  
Conductor Diameter - Minimum 0.563  
Conductor Diameter Range 0.563 - 1.14



**A Hubbell brand**

©2024 Hubbell Incorporated. All rights reserved  
FG-GH286AL-SPEC-EN | REV 6/2024