

Tie, Insulator Top

By FARGO
Catalog # [GJ602FC](#)



Composite Top Tie

*Representative Image

Features

Semi-Conductive tie provides uniform electrical field around attachment point.

General

Catalog Number	GJ602FC
Color Code	Green
EU RoHS Indicator	No
Insulator Throat Neck Type	C Neck
Material	Composite
Material - Cover and Body	Semi-Conductive covering over Rigid Black PVC
Product Category	Ties
UPC	096359310600

Dimensions

Insulator Throat Diameter - Maximum	2.75 in
Insulator Throat Diameter - Minimum	2.12 in
Insulator Throat Diameter Range	2.12 - 2.75
Length	26 in
Weight	0.314 lb

Conductor Related

Conductor Diameter (Covered) - Maximum	0.561 in
Conductor Diameter (Covered) - Minimum	0.407 in
Conductor Diameter (Covered) Range	0.561-0.407
Conductor Diameter - Maximum	0.561
Conductor Diameter - Minimum	0.407
Conductor Diameter Range	0.407 - 0.561
Conductor Type	Covered

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
--------------------------	----------------------

Logistics

Carton Quantity	100
Pallet Quantity	600

Product Assets

[Sales Drawings - GJ600 Composite Top Ties](#)
[Specifications - GJ602FC](#)