

Tie, Insulator Top

By FARGO
Catalog # [GJ625FC](#)



Composite Top Tie

*Representative Image

Features

- Semi-Conductive tie provides uniform electrical field around attachment point.

General

Color Code	Red
EU RoHS Indicator	No
Insulator Throat Neck Type	J Neck
Material	Composite
Material - Cover and Body	Semi-Conductive covering over Rigid Black PVC
Product Category	Ties
UPC	096359356271

Dimensions

Insulator Throat Diameter - Maximum	4 in
Insulator Throat Diameter - Minimum	3.38 in
Insulator Throat Diameter Range	3.38 - 4
Length	26.000 in
Weight	0.372 lb

Conductor Related

Conductor Diameter (Covered) - Maximum	1.125 in
Conductor Diameter (Covered) - Minimum	0.92 in
Conductor Diameter (Covered) Range	1.125-0.92
Conductor Diameter - Maximum	1.125
Conductor Diameter - Minimum	0.92
Conductor Diameter Range	0.92 - 1.125
Conductor Type	Covered

Logistics

Carton Quantity	75
-----------------	----

Product Assets

[Sales Drawings - GJ600 Composite Top Ties](#)