

Tie, Double Arm

By FARGO
Catalog # [GJ802FC](#)



Composite Double Pin Tie

*Representative Image

Features

Semi-Conductive tie provides uniform electrical field around attachment point.

General

Catalog Number	GJ802FC
Color Code	Green
EU RoHS Indicator	No
Insulator Throat Neck Type	C Neck
Material	Composite
Material - Cover and Body	Semi-Conductive covering over Rigid Black PVC
Product Category	Ties
UPC	096359310877

Dimensions

Insulator Throat Diameter - Maximum	2.75 in
Insulator Throat Diameter - Minimum	2.12 in
Insulator Throat Diameter Range	2.12 - 2.75
Length	13 in
Weight	0.323 lb

Conductor Related

Conductor Diameter (Covered) - Maximum	0.561 in
Conductor Diameter (Covered) - Minimum	0.407 in
Conductor Diameter (Covered) Range	0.561-0.407
Conductor Diameter - Maximum	0.561
Conductor Diameter - Minimum	0.407
Conductor Diameter Range	0.407 - 0.561
Conductor Type	Covered

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
--------------------------	----------------------

Logistics

Carton Quantity	100
Pallet Quantity	600

Product Assets

[Sales Drawings - CC-26432](#)
[Specifications - GJ802FC](#)