

Tie, Double Arm

By FARGO
Catalog # [GJ813FC](#)



Composite Double Pin Tie

*Representative Image

Features

- Semi-Conductive tie provides uniform electrical field around attachment point.

General

Color Code	Blue
EU RoHS Indicator	No
Insulator Throat Neck Type	F Neck
Material	Composite
Material - Cover and Body	Semi-Conductive covering over Rigid Black PVC
Product Category	Ties
UPC	096359310921

Dimensions

Insulator Throat Diameter - Maximum	3.38 in
Insulator Throat Diameter - Minimum	2.75 in
Insulator Throat Diameter Range	2.75 - 3.38
Length	13.250 in
Weight	0.353 lb

Conductor Related

Conductor Diameter (Covered) - Maximum	0.717 in
Conductor Diameter (Covered) - Minimum	0.562 in
Conductor Diameter (Covered) Range	0.717-0.562
Conductor Diameter - Maximum	0.717
Conductor Diameter - Minimum	0.562
Conductor Diameter Range	0.562 - 0.717
Conductor Type	Covered

Logistics

Carton Quantity	100
Pallet Quantity	600

Product Assets

[Sales Drawings - CC-26432](#)