

Automatic Splice Copper

By FARGO  
Catalog # [GL117](#)

Automatic Splice, for 2/0 SOL or 1/0 (7 str), #1 (3 str) Copper,  
2A Copperweld, Dia. Range 0.36 - 0.37 in.



\*Representative Image

Features

- Fastest method of splicing copper and copperweld conductor
- Individually bagged to seal out dirt before use
- Inhibitor protected for optimum long term performance
- ANSI C19.4 Class 1A Normal tension Connector (60% RBS)

General

Catalog Number	GL117
Color Code	None
EU RoHS Indicator	Contact Manufacturer
Material	Copper
Material - Gripping Unit	Bronze Alloy
UPC	096359311416

Dimensions

Dimensions	5.500 in x 0.940 in x 0.940 in
Height	0.94 in
Length	5.5 in
Weight	0.53 lb
Width	0.94 in

Conductor Related

Conductor Diameter - Maximum	0.37
Conductor Diameter - Minimum	0.36
Conductor Diameter Range	0.36 - 0.37
Conductor Type	Copper, Copperweld

Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2024)
UL Listed	No

Logistics

Pallet Quantity	3600
-----------------	------

Product Assets

- [Catalogs - Distribution Connectors](#)
- [Sales Drawings - Sales Drawing](#)
- [Specifications - GL117](#)