

Automatic Splice, Aluminum, Full Tension

By FARGO
Catalog # [GL1333A](#)



Automatic Splice, 10,000 Lb, for 636 AAC, 556.5 18/1 ACSR,
Dia. Range 0.84 - 0.92 in.

*Representative Image

Features

- ANSI C119.4
- Class A connector
- Maximum design rating 10,000 lb/44.5 kN
- Color coded funnel guides for easy installation

General

Color Code	Natural
Material	Aluminum Alloy
Trade Name	Fargo
UPC	096359311621

Dimensions

Dimensions	15.000 in x 2.000 in x 2.000 in
Height	2.000 in
Length	15.000 in
Weight	1.960 lb
Width	2.000 in

Conductor Related

Conductor Compatibility	ACSR-Flicker-477-24/7;ACSR-Hawk-477-26/7;ACSR-Hen-477-30/7;ACSR-Osprey-556.5-18/1;ACSR-Parakeet-556.5-24/7;AAC-Dahlia-556.5-19;AAC-Mistletoe-556.5-37;AAC-Meadowsweet-600-37;AAC-Orchid-636-37
Conductor Diameter - Maximum	0.92 in
Conductor Diameter - Minimum	0.84 in
Conductor Diameter Range	0.84 - 0.92
Conductor Type	AAC, AAAC, ACSR

Certifications and Compliance

UL Listed	No
-----------	----

Logistics

Pallet Quantity	840
-----------------	-----

Product Assets

[Catalogs - Distribution Connectors \(CA05127E\)](#)
[Sales Drawings - CC-25273](#)