

Automatic Splice, Aluminum, Full Tension

By FARGO
Catalog # [GL1333AKR](#)

Automatic Splice, Corrosion Resistant, 10,000 Lb, for 636 AAC, 556.5 (18/1 STR) ACSR, Dia. Range 0.84 - 0.92 in.



*Representative Image

Features

- ANSI C119.4 Class A Connector
- Full tension (95% of conductor rated breaking strength unless otherwise noted)
- Color coded funnel guides for easy identification
- Individually bagged to seal out dirt before use.
- Corrosion Resistant

General

Color Code	Natural
Material	Aluminum Alloy
UPC	096359463634

Dimensions

Dimensions	15.000 in x 2.000 in x 2.000 in
Height	2.000 in
Length	15.000 in
Weight	1.766 lb
Width	2.000 in

Conductor Related

Conductor Diameter - Maximum	0.92 in
Conductor Diameter - Minimum	0.84 in
Conductor Diameter Range	0.84 - 0.92
Conductor Type	AAC, AAAC, ACSR

Certifications and Compliance

UL Listed	No
-----------	----

Logistics

Pallet Quantity	840
-----------------	-----

Product Assets

[Catalogs - Distribution Connectors \(CA05127E\)](#)
[Sales Drawings - GL1333AKR_drawing](#)