

# Automatic Splice, Aluminum, Full Tension

By FARGO  
Catalog # [GL1351A](#)



Automatic Splice, 10,000 Lb, for 652.8 AAC, 556.6 (26/7) ACSR, Dia. Range .927 - .940 in.

\*Representative Image

## Features

- ANSI C119.4
- Class A connector
- Maximum design rating 10,000 lb/44.5 kN
- Color coded funnel guides for easy installation

## General

Color Code	Natural
Material	Aluminum Alloy
Trade Name	Fargo
UPC	096359311645

## Dimensions

Weight	1.960 lb
--------	----------

## Conductor Related

Conductor Compatibility	ACSR-Dove-556.5-26/7
Conductor Diameter - Maximum	0.927 in
Conductor Diameter - Minimum	0.927 in
Conductor Diameter Range	0.927 - 0.927
Conductor Type	AAC, AAAC, ACSR

## Certifications and Compliance

UL Listed	No
-----------	----

## Logistics

Pallet Quantity	840
-----------------	-----

## Product Assets

[Catalogs - Distribution Connectors \(CA05127E\)](#)  
[Sales Drawings - Overhead\\_line\\_Splices\\_Automatic\\_Aluminum\(CC-25273\)](#)