

HUBBELL

Power Systems

Automatic Splice, Aluminum, Full Tension

By FARGO
Catalog # [GL1355AKR](#)

Automatic Splice, Corrosion Resistant, 10,000 Lb, for 700, 715 AAC, Dia. Range 0.94 - 0.976 in.



*Representative Image

Features

- ANSI C119.4 Class A Connector
- Full tension (95% of conductor rated breaking strength unless otherwise noted)
- Color coded funnel guides for easy identification
- Individually bagged to seal out dirt before use.
- Corrosion Resistant

General

Color Code	Natural
Material	Aluminum Alloy
UPC	096359576976

Conductor Related

Conductor Diameter - Maximum	0.976 in
Conductor Diameter - Minimum	0.94 in
Conductor Diameter Range	0.94 - 0.976
Conductor Type	AAC, AAAC, ACSR

Certifications And Compliance

UL Listed	No
-----------	----

Logistics

Pallet Quantity	840
-----------------	-----

Product Assets

[Sales Drawings - GL1355AKR_drawing](#)