

HUBBELL

Power Systems

Automatic Splice, Aluminum, Full Tension

By FARGO
Catalog # [GL1441AKR](#)

Automatic Splice, Corrosion Resistant, 10,000 Lb, for 954 AAC,
Dia. Range 1.100 - 1.140 in.



*Representative Image

Features

- ANSI C119.4 Class A Connector
- Full tension (95% of conductor rated breaking strength unless otherwise noted)
- Color coded funnel guides for easy identification
- Individually bagged to seal out dirt before use.
- Corrosion Resistant

General

Color Code	Red
Material	Aluminum Alloy
UPC	096359576990

Conductor Related

Conductor Diameter - Maximum	1.14 in
Conductor Diameter - Minimum	1.1 in
Conductor Diameter Range	1.1 - 1.14
Conductor Type	AAC, AAAC, ACSR

Certifications And Compliance

UL Listed	No
-----------	----

Logistics

Pallet Quantity	840
-----------------	-----

Product Assets