

HUBBELL

Power Systems

Automatic Splice, Aluminum, Full Tension

By FARGO
Catalog # [GL404A](#)

Automatic Splice, Full Tension, for #2 ACSR/AAAC/AAC. Dia Range .280 - .320 in.



*Representative Image

Features

- ANSI C119.4
- Class A connector
- Full tension (95% of conductor rated breaking strength unless noted otherwise)
- Color coded funnel guides for easy identification
- Individually bagged to seal out dirt before use

General

Color Code	Red
Material	Aluminum Alloy
Trade Name	Fargo
UPC	096359311973

Dimensions

Dimensions	12.000 in x 1.000 in x 1.000 in
Height	1 in
Length	12 in
Weight	0.412 lb
Width	1 in

Conductor Related

Conductor Compatibility	ACSR-Sparrow-2-6/1;AAC-Iris-2-7;AAAC 6201 Alloy-Ames-77.47-6/18
Conductor Diameter - Maximum	0.32 in
Conductor Diameter - Minimum	0.28 in
Conductor Diameter Range	0.28 - 0.32
Conductor Type	AAC, AAAC, ACSR

Certifications And Compliance

UL Listed	No
-----------	----

Logistics

Pallet Quantity	3200
-----------------	------

Product Assets

- [Catalogs - Distribution Connectors](#)
- [Literature - Quick Reference Guide: Splices for Overhead Connections](#)
- [Sales Drawings - GL4xx_DRAWING](#)
- [Video - Hubbell Power Systems Automatic Splice Installation](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
FG-GL404A-SPEC-EN | REV 6/2024