

Automatic Splice, Aluminum, Full Tension

By FARGO
Catalog # [GL404AKR](#)

Automatic Splice, Corrosion Resistant, Full Tension, for #2 ACSR/AAAC/AAC. Dia Range .280 - .320 in.



*Representative Image

Features

- ANSI C119.4
- Class A connector
- Full tension (95% of conductor rated breaking strength unless noted otherwise)
- Color coded funnel guides for easy identification

General

Color Code	Red
Material	Aluminum Alloy
UPC	096359505594

Conductor Related

Conductor Diameter - Maximum	0.32 in
Conductor Diameter - Minimum	0.28 in
Conductor Diameter Range	0.28 - 0.32
Conductor Type	AAC, AAAC, ACSR

Certifications and Compliance

UL Listed	No
-----------	----

Logistics

Carton Quantity	25
Pallet Quantity	3200

Product Assets

[Literature - Quick Reference Guide: Splices for Overhead Connections \(LEEDS-HPS-SPLICES-QUICK-REFERENCE-GUIDE-SF-EN-2023\)](#)

[Sales Drawings - GL404AKR_drawing](#)

[Video - Hubbell Power Systems Automatic Splice Installation \(V10548E\)](#)