

Automatic Splice, Aluminum, Full
Tension

By FARGO
Catalog # [GL406A](#)



Automatic Splice, Full Tension, for 1/0 ACSR/AAAC/AAC. Dia.
Range .355 - .400 in

*Representative Image

Features

- ANSI C119.4
- Class A connector
- Full tension (95% of conductor rated breaking strength unless noted otherwise)
- Color coded funnel guides for easy identification
- Individually bagged to seal out dirt before use

General

Catalog Number	GL406A
Color Code	Yellow
Material	Aluminum Alloy
Trade Name	Fargo
UPC	096359312017

Dimensions

Dimensions	12.000 in x 1.100 in x 1.100 in
Height	1.1 in
Length	12 in
Weight	0.441 lb
Width	1.1 in

Conductor Related

Conductor Compatibility	ACSR-Robin-1-6/1;ACSR-Raven-1/0-6/1;AAC-Poppy-1/0-7;AAAC 6201 Alloy-Azusa-123.3-6/18
Conductor Diameter - Maximum	0.4 in
Conductor Diameter - Minimum	0.355 in
Conductor Diameter Range	0.355 - 0.4
Conductor Type	AAC, AAAC, ACSR

Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2025)
UL Listed	No

Logistics

Pallet Quantity	2400
-----------------	------

Product Assets

- [Catalogs - Distribution Connectors](#)
- [Literature - Quick Reference Guide: Splices for Overhead Connections](#)
- [Sales Drawings - GL4xx_DRAWING](#)
- [Specifications - GL406A](#)
- [Video - Hubbell Power Systems Automatic Splice Installation](#)