

# HUBBELL

## Power Systems

### Automatic Splice, Aluminum, Full Tension

By FARGO  
Catalog # [GL406AKR](#)

Automatic Splice, Corrosion Resistant, Full Tension, for 1/0 ACSR/AAAC/AAC. Dia. Range .355 - .400 in



\*Representative Image

#### Features

- ANSI C119.4
- Class A connector
- Full tension (95% of conductor rated breaking strength unless noted otherwise)
- Color coded funnel guides for easy identification

#### General

Color Code	Yellow
Material	Aluminum Alloy
UPC	096359505600

#### Dimensions

Dimensions	12.000 in x 1.100 in x 1.100 in
Height	1.1 in
Length	12 in
Weight	0.419 lb
Width	1.1 in

#### Conductor Related

Conductor Diameter - Maximum	0.4 in
Conductor Diameter - Minimum	0.355 in
Conductor Diameter Range	0.355 - 0.4
Conductor Type	AAC, AAAC, ACSR

#### Certifications And Compliance

UL Listed	No
-----------	----

#### Logistics

Pallet Quantity	2400
-----------------	------

#### Product Assets

[Catalogs - Distribution Connectors](#)  
[Literature - Quick Reference Guide: Splices for Overhead Connections](#)  
[Sales Drawings - GL406AKR\\_drawing](#)  
[Video - Hubbell Power Systems Automatic Splice Installation](#)



A Hubbell brand