

HUBBELL

Power Systems

Automatic Splice, Aluminum, Full Tension

By FARGO
Catalog # [GL407](#)

Automatic Splice, Full Tension, for 2/O ACSR/AAAC/AAC. Dia. Range .400 - .470 in



*Representative Image

Features

- ANSI C119.4 Class A Connector
- Full tension (95% of conductor rated breaking strength unless otherwise noted)
- Color coded funnel guides for easy identification
- Individually bagged to seal out dirt before use.

General

Color Code	Gray
Material	Aluminum Alloy
Trade Name	Fargo
UPC	096359312048

Dimensions

Dimensions	18.000 in x 1.400 in x 1.400 in
Height	1.4 in
Length	18 in
Weight	1.058 lb
Width	1.4 in

Conductor Related

Conductor Compatibility	ACSR-Quail-2/O-6/1;AAC-Aster-2/O-7;AAC-Phlox-3/O-7;AAAC 6201 Alloy-Anaheim-155.4-6/18
Conductor Diameter - Maximum	0.47 in
Conductor Diameter - Minimum	0.4 in
Conductor Diameter Range	0.4 - 0.47
Conductor Type	AAC, AAAC, ACSR

Certifications And Compliance

UL Listed	No
-----------	----

Logistics

Pallet Quantity	1000
-----------------	------

Product Assets

- [Catalogs - Distribution Connectors](#)
- [Literature - Quick Reference Guide: Splices for Overhead Connections](#)
- [Sales Drawings - GL4xx_DRAWING](#)
- [Video - Hubbell Power Systems Automatic Splice Installation](#)

