

Automatic Splice, Aluminum, Full Tension

By FARGO
Catalog # [GL4076A](#)

Automatic Splice, Full Tension, for 1/0 - 2/0 ACSR/AAAC/AAC.
Dia. Range .355 - .470 in



*Representative Image

Features

- ANSI C119.4 Class A Connector
- Full tension (95% of conductor rated breaking strength unless otherwise noted)
- Color coded funnel guides for easy identification
- Individually bagged to seal out dirt before use.

General

Color Code	Yellow; Gray
Material	Aluminum Alloy
Trade Name	Fargo
UPC	096359384076

Dimensions

Dimensions	18.000 in x 1.400 in x 1.400 in
Height	1.400 in
Length	18.000 in
Weight	1.058 lb
Width	1.400 in

Conductor Related

Conductor Compatibility	ACSR-Robin-1-6/1;ACSR-Raven-1/0-6/1;ACSR-Quail-2/0-6/1;AAC-Poppy-1/0-7;AAC-Aster-2/0-7;AAC-Phlox-3/0-7;AAAC 6201 Alloy-Azusa-123.3-6/18;AAAC 6201 Alloy-Anaheim-155.4-6/18
Conductor Diameter - Maximum	0.47 in
Conductor Diameter - Minimum	0.355 in
Conductor Diameter Range	0.355 - 0.47
Conductor Type	AAC, AAAC, ACSR

Certifications and Compliance

UL Listed	No
-----------	----

Logistics

Pallet Quantity	1000
-----------------	------

Product Assets

[Catalogs - Distribution Connectors \(CA05127E\)](#)
[Literature - Quick Reference Guide: Splices for Overhead Connections \(LEEDS-HPS-SPLICES-QUICK-REFERENCE-GUIDE-SF-EN-2023\)](#)
[Sales Drawings - GL4xx_DRAWING](#)
[Video - Hubbell Power Systems Automatic Splice Installation \(VI0548E\)](#)