

# HUBBELL

## Power Systems

### Automatic Splice, Aluminum, Full Tension

By FARGO  
Catalog # [GL408](#)

Automatic Splice, Full Tension, for 3/0 ACSR/AAAC/AAC. Dia. Range .450 - .530 in



\*Representative Image

#### Features

- ANSI C119.4 Class A Connector
- Full tension (95% of conductor rated breaking strength unless otherwise noted)
- Color coded funnel guides for easy identification
- Individually bagged to seal out dirt before use.

#### General

Color Code	Black
Material	Aluminum Alloy
Trade Name	Fargo
UPC	096359312055

#### Dimensions

Dimensions	20.000 in x 1.600 in x 1.600 in
Height	1.6 in
Length	20 in
Weight	1.588 lb
Width	1.6 in

#### Conductor Related

Conductor Compatibility	ACSR-Pigeon-3/0-6/1;AAC-Phlox-3/0-7;AAC-Oxlip-4/0-7;AAAC 6201 Alloy-Amherst-195.7-6/18
Conductor Diameter - Maximum	0.53 in
Conductor Diameter - Minimum	0.45 in
Conductor Diameter Range	0.45 - 0.53
Conductor Type	AAC, AAAC, ACSR

#### Certifications And Compliance

UL Listed	No
-----------	----

#### Logistics

Pallet Quantity	800
-----------------	-----

#### Product Assets

- [Catalogs - Distribution Connectors](#)
- [Literature - Quick Reference Guide: Splices for Overhead Connections](#)
- [Sales Drawings - GL4xx\\_DRAWING](#)
- [Video - Hubbell Power Systems Automatic Splice Installation](#)

