

Automatic Splice, Aluminum, Full
Tension

By FARGO
Catalog # [GL409A](#)

Automatic Splice, Full Tension, for 4/0 ACSR/AAAC/AAC. Dia.
Range .505 - .595 in



*Representative Image

Features

- ANSI C119.4 Class A Connector
- Full tension (95% of conductor rated breaking strength unless otherwise noted)
- Color coded funnel guides for easy identification
- Individually bagged to seal out dirt before use.

General

Catalog Number	GL409A
Color Code	Pink
Material	Aluminum Alloy
Trade Name	Fargo
UPC	096359312079

Dimensions

Dimensions	17.000 in x 1.600 in x 1.600 in
Height	1.6 in
Length	17 in
Weight	1.098 lb
Width	1.6 in

Conductor Related

Conductor Compatibility	ACSR-Penguin-4/0-6/1;AAC-Oxlip-4/0-7;AAC-Valerian-250-
-------------------------	--

Conductor Diameter - Maximum	19;AAC-Laurel-266.8-19;AAAC 6201 Alloy-Alliance-246.9-6/18 0.595 in
Conductor Diameter - Minimum	0.505 in
Conductor Diameter Range	0.505 - 0.595
Conductor Type	AAC, AAAC, ACSR

Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2024)
UL Listed	No

Logistics

Pallet Quantity	800
-----------------	-----

Product Assets

- [Catalogs - Distribution Connectors](#)
- [Literature - Quick Reference Guide: Splices for Overhead Connections](#)
- [Sales Drawings - GL4xx_DRAWING](#)
- [Specifications - GL409A](#)
- [Video - Hubbell Power Systems Automatic Splice Installation](#)