

Automatic Splice, Aluminum, Full
Tension

By FARGO
Catalog # [GL410](#)

Automatic Splice, Full Tension, for 336.4 AAC, 312.8 AAAC, 266.8 (18/1) ACSR, Dia. Range 0.603 - 0.666 in.



*Representative Image

Features

-
-
-
-
-

General

Catalog Number	GL410
Color Code	Brown
Material	Aluminum Alloy
Trade Name	Fargo
UPC	096359312086

Dimensions

Dimensions	19.000 in x 1.700 in x 1.700 in
Height	1.7 in
Length	19 in
Weight	1.411 lb
Width	1.7 in

Conductor Related

Conductor Compatibility	ACSR-Waxwing-266.8-18/1;AAC-Tulip-336.1-19
Conductor Diameter - Maximum	0.666 in
Conductor Diameter - Minimum	0.603 in
Conductor Diameter Range	0.603 - 0.666
Conductor Type	AAC, AAAC, ACSR

Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2024)
UL Listed	No

Logistics

Pallet Quantity	800
-----------------	-----

Product Assets

- [Catalogs - Distribution Connectors](#)
- [Literature - Quick Reference Guide: Splices for Overhead Connections](#)
- [Sales Drawings - GL4xx_DRAWING](#)
- [Specifications - GL410](#)
- [Video - Hubbell Power Systems Automatic Splice Installation](#)