

# HUBBELL

## Power Systems

### Automatic Splice, Aluminum, Full Tension

By FARGO  
Catalog # [GL410KR](#)

Automatic Splice, Corrosion Resistant, Full Tension, for 336.4 AAC, 312.8 AAAC, 266.8 (18/1) ACSR, Dia. Range 0.603 - 0.666 in.



\*Representative Image

#### Features

- ANSI C119.4 Class A Connector
- Full tension (95% of conductor rated breaking strength unless otherwise noted)
- Color coded funnel guides for easy identification
- Individually bagged to seal out dirt before use.
- Corrosion Resistant

#### General

Color Code	Brown
Material	Aluminum Alloy
UPC	096359578796

#### Conductor Related

Conductor Diameter - Maximum	0.666 in
Conductor Diameter - Minimum	0.603 in
Conductor Diameter Range	0.603 - 0.666
Conductor Type	AAC, AAAC, ACSR

#### Certifications And Compliance

UL Listed	No
-----------	----

#### Logistics

Pallet Quantity	800
-----------------	-----

#### Product Assets

- [Literature - Quick Reference Guide: Splices for Overhead Connections](#)
- [Sales Drawings - GL410KR\\_drawing](#)
- [Video - Hubbell Power Systems Automatic Splice Installation](#)