

# HUBBELL

## Power Systems

### Automatic Splice, Aluminum, Full Tension

By FARGO  
Catalog # [GL411KR](#)

Automatic Splice, Corrosion Resistant, Full Tension, for 397.5, 336.4 AAC, 394.5 AAAC, 336.4(18/1) ACSR, Dia. Range 0.659 - 0.724 in.



\*Representative Image

#### Features

- ANSI C119.4 Class A Connector
- Full tension (95% of conductor rated breaking strength unless otherwise noted)
- Color coded funnel guides for easy identification
- Individually bagged to seal out dirt before use.
- Corrosion Resistant

#### General

Color Code	Green
Material	Aluminum Alloy
UPC	096359505648

#### Dimensions

Dimensions	20.000 in x 1.800 in x 1.800 in
Height	1.8 in
Length	20 in
Weight	1.764 lb
Width	1.8 in

#### Conductor Related

Conductor Diameter - Maximum	0.724 in
Conductor Diameter - Minimum	0.659 in
Conductor Diameter Range	0.659 - 0.724
Conductor Type	AAC, AAAC, ACSR

#### Certifications And Compliance

UL Listed	No
-----------	----

#### Logistics

Carton Quantity	25
Pallet Quantity	400

#### Product Assets

- [Catalogs - Distribution Connectors](#)
- [Literature - Quick Reference Guide: Splices for Overhead Connections](#)
- [Sales Drawings - GL411KR\\_drawing](#)
- [Video - Hubbell Power Systems Automatic Splice Installation](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
FG-GL411KR-SPEC-EN | REV 6/2024