

Automatic Splice, Aluminum, Full Tension

By FARGO
Catalog # [GL412](#)

Automatic Splice, Full Tension, for 477 AAC, 465.4 AAAC, 397.5 (18/1) ACSR, Dia. Range 0.720 - 0.795 in.



*Representative Image

Features

- ANSI C119.4 Class A Connector
- Full tension (95% of conductor rated breaking strength unless otherwise noted)
- Color coded funnel guides for easy identification
- Individually bagged to seal out dirt before use.
- *Includes Compact Conductor of Same Size - ASTM-B400

General

Catalog Number	GL412
Color Code	Blue
Material	Aluminum Alloy
Trade Name	Fargo
UPC	096359312116

Dimensions

Dimensions	22.000 in x 2.000 in x 2.000 in
Height	2 in
Length	22 in
Weight	2.323 lb
Width	2 in

Conductor Related

Conductor Compatibility	ACSR-Oriole-336.4-30/7;ACSR-Chickadee-397.5-
-------------------------	--

Conductor Diameter - Maximum	18/1;ACSR-Brant-397.5-24/7;ACSR-Ibis-397.5-26/7;AAC-Canna-397.5-19;AAC-Cosmos-477-19;AAC-Syringa-477-37
Conductor Diameter - Minimum	0.72 in
Conductor Diameter Range	0.72 - 0.795
Conductor Type	AAC, AAAC, ACSR

Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2024)
UL Listed	No

Logistics

Pallet Quantity	400
-----------------	-----

Product Assets

- [Catalogs - Distribution Connectors](#)
- [Literature - Quick Reference Guide: Splices for Overhead Connections](#)
- [Sales Drawings - GL4xx_DRAWING](#)
- [Specifications - GL412](#)
- [Video - Hubbell Power Systems Automatic Splice Installation](#)