

Automatic Splice, Aluminum, Full  
Tension

By FARGO  
Catalog # [GL413](#)

Automatic Splice, Full Tension, for 556.5, 500 AAC, 559.5 AAAC,  
477 (18/1) ACSR, Dia. Range 0.78 - 0.858 in.

Features

- ANSI C119.4 Class A Connector
- Full tension (95% of conductor rated breaking strength unless otherwise noted)
- Color coded funnel guides for easy identification
- Individually bagged to seal out dirt before use.
- \*Includes Compact Conductor of Same Size - ASTM-B400

General

Catalog Number	GL413
Color Code	White
Material	Aluminum Alloy
Trade Name	Fargo
UPC	096359312147

Dimensions

Dimensions	24.000 in x 2.100 in x 2.100 in
Height	2.1 in
Length	24 in
Weight	2.842 lb
Width	2.1 in

Conductor Related

Conductor Compatibility	ACSR-Ibis-397.5-26/7;ACSR-Lark-397.5-30/7;ACSR-Pelican-
-------------------------	---



\*Representative Image

477-18/1;AAC-Cosmos-477-19;AAC-Syringa-477-37;AAC-Zinnia-500-19;AAC-Hyacinth-500-37;AAC-Dahlia-556.5-19;AAC-Mistletoe-556.5-37	
Conductor Diameter - Maximum	0.858 in
Conductor Diameter - Minimum	0.78 in
Conductor Diameter Range	0.78 - 0.858
Conductor Type	AAC, AAAC, ACSR

Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2024)
UL Listed	No

Logistics

Pallet Quantity	560
-----------------	-----

Product Assets

- [Catalogs - Distribution Connectors](#)
- [Literature - Quick Reference Guide: Splices for Overhead Connections](#)
- [Sales Drawings - GL4xx\\_DRAWING](#)
- [Specifications - GL413](#)
- [Video - Hubbell Power Systems Automatic Splice Installation](#)