

Automatic Splice, Corrosion Resistant, Full Tension, for #4 - #2 AAC, AAAC, ACSR

By FARGO
Catalog # [GLSF4042AKR](#)

Automatic Splice, Corrosion Resistant, Full Tension, for #4 - #2 AAC, AAAC, ACSR, Dia. Range 0.220 - .320 in



*Representative Image

Features

- ANSI C119.4
- Class A connector
- Full tension (95% of conductor rated breaking strength unless noted otherwise)
- Innovative design to help reduce partial tension issues
- Indicators deploy upon full conductor insertion
- Jaws remain in place until conductor is fully inserted
- Simple, smooth installation

General

Color Code	Red-Orange
Material	Aluminum Alloy
Material - Jaw	Aluminum Alloy
Trade Name	Fargo
UPC	096359610939

Dimensions

Length	13 in
Width	1.0 in

Conductor Related

Conductor Diameter - Maximum	0.32 in
Conductor Diameter - Minimum	0.22 in
Conductor Diameter Range	0.22 - 0.32
Conductor Type	<ul style="list-style-type: none">• AAC• AAAC• ACSR

Logistics

Carton Quantity	25
Pallet Quantity	3200

Product Assets

[Catalogs - Distribution Connectors \(CA05127E\)](#)
[Installation Manuals - SureFit Full-Tension Aluminum Automatic Splices](#)
[Literature - SureFit Cross Reference \(TD05059E\)](#)
[Literature - Quick Reference Guide: Splices for Overhead Connections \(LEEDS-HPS-SPLICES-QUICK-REFERENCE-GUIDE-SF-EN-2023\)](#)
[Sales Drawings - Surefit Aluminum Automatic Splice KR Version \(CC-23006\)](#)
[Sales Drawings - Surefit Aluminum Automatic Splice KR Version \(CC-23006\)](#)
[Video - In Depth: SureFit Automatic Splice \(VI05121E0518\)](#)