

## Automatic Splice, Corrosion Resistant, Full Tension, for 1/0 AAC, AAAC, ACSR

By FARGO  
Catalog # [GLSF406AKR](#)

Automatic Splice, Corrosion Resistant, Full Tension, for 1/0 AAC, AAAC, ACSR, Dia. Range .355 - .400 in



\*Representative Image

### Features

- ANSI C119.4
- Class A connector
- Full tension (95% of conductor rated breaking strength unless noted otherwise)
- Innovative design to help reduce partial tension issues
- Indicators deploy upon full conductor insertion
- Jaws remain in place until conductor is fully inserted
- Simple, smooth installation

### General

Color Code	Yellow
Material	Aluminum Alloy
Material - Jaw	Aluminum Alloy
Trade Name	Fargo
UPC	096359648079

### Dimensions

Dimensions	13.000 in x 1.000 in x 1.000 in
Height	1.000 in
Length	13.000 in
Weight	0.510 lb
Width	1.000 in

### Conductor Related

Conductor Diameter - Maximum	0.4 in
Conductor Diameter - Minimum	0.355 in
Conductor Diameter Range	0.355 - 0.4
Conductor Type	<ul style="list-style-type: none"><li>• AAC</li><li>• AAAC</li><li>• ACSR</li></ul>

### Logistics

Pallet Quantity	2400
-----------------	------

### Product Assets

[Catalogs - Distribution Connectors \(CA05127E\)](#)  
[Installation Manuals - SureFit Full-Tension Aluminum Automatic Splices](#)  
[Literature - SureFit Cross Reference \(TD05059E\)](#)  
[Literature - Quick Reference Guide: Splices for Overhead Connections \(LEEDS-HPS-SPLICES-QUICK-REFERENCE-GUIDE-SF-EN-2023\)](#)  
[Sales Drawings - Surefit Aluminum Automatic Splice KR Version \(CC-23006\)](#)  
[Sales Drawings - Surefit Aluminum Automatic Splice KR Version \(CC-23006\)](#)  
[Video - In Depth: SureFit Automatic Splice \(VI05121E0518\)](#)