

Automatic Splice, Full Tension, for  
1/0 - 2/0 AAC, AAAC, ACSR

By FARGO  
Catalog # [GLSF4076A](#)

Automatic Splice, Full Tension, for 1/0 - 2/0 AAC, AAAC, ACSR,  
Dia. Range .355 - .470 in

Features

- ANSI C119.4
- Class A connector
- Full tension (95% of conductor rated breaking strength unless noted otherwise)
- Innovative design to help reduce partial tension issues
- Indicators deploy upon full conductor insertion
- Jaws remain in place until conductor is fully inserted
- Simple, smooth installation

General

Catalog Number	GLSF4076A
Color Code	Yellow-Gray
Material	Aluminum Alloy
Material - Jaw	Aluminum Alloy
Trade Name	Fargo
UPC	096359610816

Dimensions

Dimensions	19.000 in x 1.400 in x 1.400 in
Height	1.4 in
Length	19 in
Weight	1.167 lb
Width	1.4 in

Conductor Related



Conductor Diameter - Maximum	0.47 in
Conductor Diameter - Minimum	0.355 in
Conductor Diameter Range	0.355 - 0.47
Conductor Type	<ul style="list-style-type: none"><li>• AAC</li><li>• AAAC</li><li>• ACSR</li></ul>

Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2024)
--------------------------	---

Logistics

Pallet Quantity	600
-----------------	-----

Product Assets

- [Catalogs - Distribution Connectors](#)
- [Installation Manuals - SureFit Full-Tension Aluminum Automatic Splices](#)
- [Literature - Quick Reference Guide: Splices for Overhead Connections](#)
- [Literature - SureFit Cross Reference](#)
- [Sales Drawings - Surefit Aluminum Automatic Splice](#)
- [Sales Drawings - Surefit Aluminum Automatic Splice](#)
- [Specifications - GLSF4076A](#)
- [Video - In Depth: SureFit Automatic Splice](#)
- [Video - In Depth: SureFit Automatic Splice](#)
- [Video - Fargo - SureFit Automatic Splice](#)