

Automatic Splice, Corrosion  
Resistant, Full Tension, for 3/0 -  
4/0 AAC, AAAC, ACSR

By FARGO  
Catalog # [GLSF4098KR](#)



\*Representative Image

Automatic Splice, Corrosion Resistant, Full Tension, for 3/0 - 4/0  
AAC, AAAC, ACSR, Dia. Range .450 - .595 in

Features

- ANSI C119.4
- Class A connector
- Full tension (95% of conductor rated breaking strength unless noted otherwise)
- Innovative design to help reduce partial tension issues
- Indicators deploy upon full conductor insertion
- Jaws remain in place until conductor is fully inserted
- Simple, smooth installation

General

Catalog Number	GLSF4098KR
Color Code	Pink-Black
Material	Aluminum Alloy
Material - Jaw	Aluminum Alloy
Trade Name	Fargo
UPC	096359610847

Dimensions

Dimensions	23.000 in x 1.700 in x 1.700 in
Height	1.7 in
Length	23 in
Weight	2.064 lb
Width	1.7 in

Conductor Related

Conductor Diameter - Maximum	0.595 in
---------------------------------	----------

Conductor Diameter - Minimum	0.45 in
Conductor Diameter Range	0.45 - 0.595
Conductor Type	<ul style="list-style-type: none"><li>• AAC</li><li>• AAAC</li><li>• ACSR</li></ul>

Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2024)
--------------------------	--

Logistics

Carton Quantity	25
Pallet Quantity	1000

Product Assets

- [Catalogs - Distribution Connectors](#)
- [Installation Manuals - SureFit Full-Tension Aluminum Automatic Splices](#)
- [Literature - Quick Reference Guide: Splices for Overhead Connections](#)
- [Literature - SureFit Cross Reference](#)
- [Sales Drawings - Surefit Aluminum Automatic Splice KR Version](#)
- [Sales Drawings - Surefit Aluminum Automatic Splice KR Version \(CC-23006\)](#)
- [Specifications - GLSF4098KR](#)
- [Video - In Depth: SureFit Automatic Splice](#)
- [Video - In Depth: SureFit Automatic Splice](#)