

Automatic Splice, Corrosion
Resistant, Full Tension, for *336.4,
*397.5 AAC, 394.5 AAAC, 336.4 18/1
ACSR

By FARGO
Catalog # [GLSF411KR](#)

Automatic Splice, Corrosion Resistant, Full Tension, for *336.4,
*397.5 AAC, 394.5 AAAC, 336.4 18/1 ACSR, Dia. Range .659 -
.724 in

Features

- ANSI C119.4
- Class A connector
- Full tension (95% of conductor rated breaking strength unless noted otherwise)
- Innovative design to help reduce partial tension issues
- Indicators deploy upon full conductor insertion
- Jaws remain in place until conductor is fully inserted
- Simple, smooth installation

General

Catalog Number	GLSF411KR
Color Code	Green
Material	Aluminum Alloy
Trade Name	Fargo
UPC	096359610885

Dimensions

Dimensions	21.000 in x 1.800 in x 1.800 in
Height	1.8 in
Length	21 in
Weight	2 lb
Width	1.8 in

Conductor Related

Conductor Diameter - Maximum	0.724 in
---------------------------------	----------



*Representative Image

Conductor Diameter - Minimum	0.659 in
Conductor Diameter Range	0.659 - 0.724
Conductor Type	<ul style="list-style-type: none">• AAC• AAAC• ACSR

Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2024)
--------------------------	--

Logistics

Pallet Quantity	400
-----------------	-----

Product Assets

- [Catalogs - Distribution Connectors](#)
- [Installation Manuals - SureFit Full-Tension Aluminum Automatic Splices](#)
- [Literature - Quick Reference Guide: Splices for Overhead Connections](#)
- [Literature - SureFit Cross Reference](#)
- [Sales Drawings - Surefit Aluminum Automatic Splice KR Version](#)
- [Sales Drawings - Surefit Aluminum Automatic Splice KR Version \(CC-23006\)](#)
- [Specifications - GLSF411KR](#)
- [Video - In Depth: SureFit Automatic Splice](#)
- [Video - In Depth: SureFit Automatic Splice](#)