

Automatic Splice, Full Tension, for
*477 AAC, 465.4 AAAC, 397.5 (18/1)
ACSR

By FARGO
Catalog # [GLSF412](#)

Automatic Splice, Full Tension, for *477 AAC, 465.4 AAAC, 397.5 (18/1) ACSR, Dia. Range .720 - .795 in

Features

- ANSI C119.4
- Class A connector
- Full tension (95% of conductor rated breaking strength unless noted otherwise)
- Innovative design to help reduce partial tension issues
- Indicators deploy upon full conductor insertion
- Jaws remain in place until conductor is fully inserted
- Simple, smooth installation

General

Catalog Number	GLSF412
Color Code	Blue
Material	Aluminum Alloy
Trade Name	Fargo
UPC	096359610892

Dimensions

Dimensions	23.000 in x 2.000 in x 2.000 in
Height	2 in
Length	23 in
Weight	1.719 lb
Width	2 in

Conductor Related



Conductor Diameter - Maximum	0.795 in
Conductor Diameter - Minimum	0.72 in
Conductor Diameter Range	0.72 - 0.795
Conductor Type	<ul style="list-style-type: none">• AAC• AAAC• ACSR

Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2024)
--------------------------	---

Logistics

Pallet Quantity	480
-----------------	-----

Product Assets

- [Catalogs - Distribution Connectors](#)
- [Installation Manuals - SureFit Full-Tension Aluminum Automatic Splices](#)
- [Literature - Quick Reference Guide: Splices for Overhead Connections](#)
- [Literature - SureFit Cross Reference](#)
- [Sales Drawings - Surefit Aluminum Automatic Splice](#)
- [Sales Drawings - Surefit Aluminum Automatic Splice](#)
- [Specifications - GLSF412](#)
- [Video - In Depth: SureFit Automatic Splice](#)
- [Video - In Depth: SureFit Automatic Splice](#)