

Automatic Splice, Corrosion Resistant, Full Tension, for *477 AAC, 465.4 AAAC, 397.5 (18/1) ACSR

By FARGO
Catalog # [GLSF412KR](#)



Automatic Splice, Corrosion Resistant, Full Tension, for *477 AAC, 465.4 AAAC, 397.5 (18/1) ACSR, Dia. Range .720 - .795 in

*Representative Image

Features

- ANSI C119.4
- Class A connector
- Full tension (95% of conductor rated breaking strength unless noted otherwise)
- Innovative design to help reduce partial tension issues
- Indicators deploy upon full conductor insertion
- Jaws remain in place until conductor is fully inserted
- Simple, smooth installation

General

Color Code	Blue
Material	Aluminum Alloy
Trade Name	Fargo
UPC	096359610908

Dimensions

Dimensions	23.000 in x 2.000 in x 2.000 in
Height	2.000 in
Length	23.000 in
Weight	2.333 lb
Width	2.000 in

Conductor Related

Conductor Diameter - Maximum	0.795 in
Conductor Diameter - Minimum	0.72 in
Conductor Diameter Range	0.72 - 0.795
Conductor Type	<ul style="list-style-type: none"> • AAC • AAAC • ACSR

Logistics

Pallet Quantity	480
-----------------	-----

Product Assets

- [Catalogs - Distribution Connectors \(CA05127E\)](#)
- [Installation Manuals - SureFit Full-Tension Aluminum Automatic Splices](#)
- [Literature - SureFit Cross Reference \(TD05059E\)](#)
- [Literature - Quick Reference Guide: Splices for Overhead Connections \(LEEDS-HPS-SPLICES-QUICK-REFERENCE-GUIDE-SF-EN-2023\)](#)
- [Sales Drawings - Surefit Aluminum Automatic Splice KR Version \(CC-23006\)](#)
- [Sales Drawings - Surefit Aluminum Automatic Splice KR Version \(CC-23006\)](#)
- [Video - In Depth: SureFit Automatic Splice \(VI05121E0518\)](#)