

Auto Splice, Corrosion Resistant,
Full Tension for 795 (37str) AAC,
795 (36/1) ACSR

By FARGO
Catalog # [GLSF414KR](#)

Auto Splice, Corrosion Resistant, Full Tension for 795 (37str)
AAC, 795 (36/1) ACSR, Dia. Range 1.026 - 1.04 in

Features

- ANSI C119.4
- Class A connector
- Full tension (95% of conductor rated breaking strength unless noted otherwise)
- Innovative design to help reduce partial tension issues
- Indicators deploy upon full conductor insertion
- Jaws remain in place until conductor is fully inserted
- Simple, smooth installation

General

Catalog Number	GLSF414KR
Color Code	Natural
Material	Aluminum Alloy
Trade Name	Fargo
UPC	096359665885

Dimensions

Length	27 in
Width	2.3 in

Conductor Related

Conductor Diameter - Maximum	1.041 in
Conductor Diameter - Minimum	1.026 in



*Representative Image

Conductor Diameter Range	1.026 - 1.041
Conductor Type	<ul style="list-style-type: none">• AAC• AAAC• ACSR

Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2024)
--------------------------	---

Logistics

Pallet Quantity	224
-----------------	-----

Product Assets

- [Catalogs - Distribution Connectors](#)
- [Installation Manuals - SureFit Full-Tension Aluminum Automatic Splices](#)
- [Literature - Quick Reference Guide: Splices for Overhead Connections](#)
- [Literature - SureFit Cross Reference](#)
- [Sales Drawings - Surefit Aluminum Automatic Splice KR Version](#)
- [Sales Drawings - Surefit Aluminum Automatic Splice KR Version \(CC-23006\)](#)
- [Specifications - GLSF414KR](#)
- [Video - In Depth: SureFit Automatic Splice](#)
- [Video - In Depth: SureFit Automatic Splice](#)