


Formed Wire Top Tie, C-Neck Insulator

By FARGO
Catalog # [LDIC4012AS](#)

C-Neck Insulator Top Tie for 556.5 and 636 ACSR, 636 and 700 AAC



Features

- For securing bare or plastic jacketed conductor in the top groove of interchangeable headstyle insulators.
- C-Neck insulator: 2-1/4" neck diameter
- Recommended for use with ANSI Class 55-2 Pin & 55-3 Pin Insulators.

Application

Top Tie

General

Color Code	Blue
EU RoHS Indicator	No
Insulator Throat Neck Type	C Neck
Material	Aluminum Clad Steel
Product Category	Ties
Type	Formed Wire
UPC	096359452942

Dimensions

Length	34.0 in
Weight	.400 lb

Conductor Related

Conductor Diameter - Maximum	0.968
Conductor Diameter - Minimum	0.859
Conductor Diameter Range	0.859 - 0.968
Conductor Type	ACSR, AAC, AAAC, Compacted ACSR, Compacted AAC and AWAC®

Logistics

Carton Quantity	50
Pallet Quantity	800

Product Assets

[Sales Drawings - LDIC, LDIF, LDIJ Top Tie Drawing](#)
[Sales Drawings - LDIC_CC-26966](#)
[Video - Hubbell Power Systems Distribution Top Tie Installation \(VI05008E\)](#)