

## Formed Wire Double Top Tie, C & F Neck Insulator

By FARGO  
Catalog # [LDID0001](#)

C & F Neck Insulator Double Top Tie for #2 and #1 ACSR, #1 AAC and #2 AAAC



### Features

- For securing the conductor in the top groove of the insulator on line angles less than 10 degrees with the insulator in a vertical orientation.
- C-Neck (2-1/4" neck diameter) & F-Neck (2-7/8" neck diameter) interchangeable headstyle insulators
- Recommended for use with ANSI Class 55-2 Pin, 55-3 Pin, 55-4 Pin, 55-5 Pin, 57-1 Post, 57-2 Post, & 57-3 Post Insulators.

### Application

Double Top Tie

### General

Color Code	Red
EU RoHS Indicator	No
Insulator Throat Neck Type	C & F Neck
Material	Aluminum Clad Steel
Product Category	Ties
Type	Formed Wire
UPC	096359452621

### Dimensions

Length	14.0 in
Weight	.300 lb

### Conductor Related

Conductor Diameter - Maximum	0.357
Conductor Diameter - Minimum	0.316
Conductor Diameter Range	0.316 - 0.357
Conductor Type	ACSR, AAC, AAAC, Compacted ACSR, Compacted AAC and AWAC®

### Logistics

Carton Quantity	50
Pallet Quantity	600

### Product Assets

[Sales Drawings - LDIDO Double Top Tie C F-Neck Drawing](#)  
[Video - Hubbell Power Systems Double Support Tie Installation \(VI05010E\)](#)