

HUBBELL

Power Systems

Formed Wire Double Top Tie, C & F Neck Insulator

By FARGO
Catalog # [LDID0040](#)



C & F Neck Insulator Double Top Tie for 4/0 ACSR, 4/0 and 266.8 AAC and 4/0 AAAC

Features

- For securing the conductor in the top groove of the insulator on line angles less than 10 degrees with the insulator in a vertical orientation.
- C-Neck (2-1/4" neck diameter) & F-Neck (2-7/8" neck diameter) interchangeable headstyle insulators
- Recommended for use with ANSI Class 55-2 Pin, 55-3 Pin, 55-4 Pin, 55-5 Pin, 57-1 Post, 57-2 Post, & 57-3 Post Insulators.

General

Application	Double Top Tie
Color Code	Red
EU RoHS Indicator	No
Insulator Throat Neck Type	C & F Neck
Material	Aluminum Clad Steel
Product Category	Ties
Type	Formed Wire
UPC	096359452652

Dimensions

Length	17 in
Weight	.460 lb

Conductor Related

Conductor Diameter - Maximum	0.588
Conductor Diameter - Minimum	0.521
Conductor Diameter Range	0.521 - 0.588
Conductor Type	ACSR, AAC, AAAC, Compacted ACSR, Compacted AAC and AWAC®

Logistics

Carton Quantity	50
Pallet Quantity	800

Product Assets

[Sales Drawings - LDID0 Double Top Tie C F-Neck Drawing](#)
[Video - Hubbell Power Systems Double Support Tie Installation](#)



A Hubbell brand