

HUBBELL

Power Systems

Formed Wire Double Top Tie, J-Neck Insulator

By FARGO
Catalog # [LDID2266](#)



J-Neck Insulator Double Top Tie for 266.8 ACSR; 266.8 and 336.4 AAC

Features

- For securing the conductor in the top groove of the insulator on line angles less than 10 degrees with the insulator in a vertical orientation.
- J-Neck (3-1/2" neck diameter) interchangeable headstyle insulator
- Recommended for use with ANSI Class 55-6 Single Skirt Pin, 55-7 Single Skirt Pin & 56-1 Double Skirt Pin Insulators.

General

Application	Double Top Tie
Color Code	Purple
Insulator Throat Neck Type	J Neck
Material	Aluminum Clad Steel
Product Category	Ties
Type	Formed Wire
UPC	096359475156

Dimensions

Length	18 in
Weight	.500 lb

Conductor Related

Conductor Diameter - Maximum	0.665
Conductor Diameter - Minimum	0.589
Conductor Diameter Range	0.589 - 0.665
Conductor Type	ACSR, AAC, AAAC, Compacted ACSR, Compacted AAC and AWAC®

Logistics

Carton Quantity	50
Pallet Quantity	800

Product Assets

[Sales Drawings - LDID2 Double Top Tie J-Neck Drawing](#)
[Video - Hubbell Power Systems Double Support Tie Installation](#)



A Hubbell brand