

HUBBELL

Power Systems

Formed Wire Top Tie, J-Neck Insulator

By FARGO
Catalog # [LDIJ4604AS](#)



J-Neck Insulator Top Tie for #2 and #1 ACSR and #2 AAAC

Features

- For securing bare or plastic jacketed conductor in the top groove of interchangeable headstyle insulators.
- J-Neck insulator: 3-1/2" neck diameter
- Recommended for use with ANSI Class 55-6, 55-7 & 56-1 Pin Insulators.

General

Application	Top Tie
Color Code	Red
EU RoHS Indicator	No
Insulator Throat Neck Type	J Neck
Material	Aluminum Clad Steel
Product Category	Ties
Type	Formed Wire
UPC	096359452577

Dimensions

Length	32 in
Weight	.290 lb

Conductor Related

Conductor Diameter - Maximum	0.357
Conductor Diameter - Minimum	0.316
Conductor Diameter Range	0.316 - 0.357
Conductor Type	ACSR, AAC, AAAC, Compacted ACSR, Compacted AAC and AWAC®

Logistics

Carton Quantity	100
Pallet Quantity	1600

Product Assets

[Sales Drawings - LDIC, LDIF, LDIJ Top Tie Drawing](#)
[Sales Drawings - LDIJ_CC-26965](#)
[Video - Hubbell Power Systems Distribution Top Tie Installation](#)



A Hubbell brand