


HUBBELL Power Systems

Formed Wire Spool Tie

By FARGO

Catalog # [LRO4012AS](#)

Spool Tie for #2 and #1 ACSR, #1 AAC, #2 AAAC- #4 and #2 Plastic Jacketed



Features

- For securing the conductor in the side groove of horizontally or vertically mounted spool insulators.
- For 1-3/4" neck diameter interchangeable headstyle insulators
- Recommended for use with ANSI Class 53-1, 53-2 & 53-3 Spool Insulators.

Application

Spool Tie

General

Catalog Number	LRO4012AS
Color Code	Red
EU RoHS Indicator	No
Insulator Throat Neck Type	Spool
Material	Aluminum Clad Steel
Product Category	Ties
Type	Formed Wire
UPC	096359452539

Dimensions

Length	24 in
Weight	.230 lb

Conductor Related

Conductor Diameter - Maximum	0.357
Conductor Diameter - Minimum	0.316
Conductor Diameter Range	0.316 - 0.357
Conductor Type	ACSR, AAC, AAAC, ACAR, Compacted ACSR and AWAC®

Logistics

Carton Quantity	100
Pallet Quantity	2000

Product Assets

[Sales Drawings - LRO Drawing](#)

[Specifications - LRO4012AS](#)

[Video - Hubbell Power Systems - Spool Tie Installation](#)

[Video - Hubbell Power Systems Quick Spool Tie Installation](#)