

Formed Wire Spool Tie

By FARGO
Catalog # [LRO4022AS](#)



Spool Tie for 3/0 ACSR, 3/0 AAC, 3/0 AAAC- #4, #1 and 1/0 Plastic Jacketed

Features

- For securing the conductor in the side groove of horizontally or vertically mounted spool insulators.
- For 1-3/4” neck diameter interchangeable headstyle insulators
- Recommended for use with ANSI Class 53-1, 53-2 & 53-3 Spool Insulators.

Application

Spool Tie

General

Catalog Number	LRO4022AS
Color Code	Orange
EU RoHS Indicator	No
Insulator Throat Neck Type	Spool
Material	Aluminum Clad Steel
Product Category	Ties
Type	Formed Wire
UPC	096359467847

Dimensions

Length	31 in
--------	-------

Weight	.320 lb
--------	---------

Conductor Related

Conductor Diameter - Maximum	0.52
Conductor Diameter - Minimum	0.46
Conductor Diameter Range	0.46 - 0.52
Conductor Type	ACSR, AAC, AAAC, ACAR, Compacted ACSR and AWAC®

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
--------------------------	----------------------

Logistics

Carton Quantity	100
Pallet Quantity	2000

Product Assets

- [Sales Drawings - LRO Drawing](#)
- [Specifications - LRO4022AS](#)
- [Video - Hubbell Power Systems - Spool Tie Installation](#)
- [Video - Hubbell Power Systems Quick Spool Tie Installation](#)