

Tee, Aluminum Compression

By FARGO
Catalog # [ORT221515](#)

"Weldment Tees, Connecting Tube to Tube at 15 degrees, Tubing Main-IPS/EHIPS-2", Tubing Tap-IPS/EHIPS-1", Material: Castings- Aluminum Alloy"



*Representative Image

Features

- "Tees are EHV rated where conductor dia. is 1" or larger"

General

EU RoHS Indicator	No
Material	Aluminum
Type	Tee, Aluminum Compression
UPC	096359451976

Dimensions

Run Length before Compression	20.1 in
Tap Length before Compression	7.2 in
Weight	5.200 lb

Conductor Related

Conductor Compatibility	ACSR-Grackle-1192.5-54/19;ACSR-Bittern-1272-45/7;ACSR-Pheasant-1272-54/19;ACSR-Dipper-1351.5-45/7;AAC-Columbine-1351.5-61;AAC-Carnation-1431-61;AAC-Gladiolus-1510.5-61
Conductor Diameter (Main) - Maximum	1.33 in
Conductor Diameter (Main) - Minimum	1.236 in
Conductor Diameter (Main) Range	1.236 - 1.33
Conductor Diameter (Tap) - Maximum	1.33 in
Conductor Diameter (Tap) - Minimum	1.236 in
Conductor Diameter (Tap) Range	1.236 - 1.33
Conductor Type	<ul style="list-style-type: none"> • AAC • ACSR

Logistics

Carton Quantity	3
Pallet Quantity	60

Product Assets

[Catalogs - Substation Connectors \(SA\)](#)