

HUBBELL

Power Systems

SUPER TOP TIE™ Formed Wire Top Tie

By FARGO
Catalog # [STT100](#)

SUPER TOP TIE™ for 266.8 ACSR, 266.8 AAC and 266.8 AAAC



Features

- SUPER TOP TIE™ ties are used for securing the conductor in the top groove of vertical-mounted C, F and J-Neck interchangeable headstyle insulators and many non-standard pin and post insulators (single- or double-support) or on *ANSI 53-2 spool insulators (horizontal or vertical).
- Semiconductor-rubber pad and high-density polyethylene on loops protect against abrasion of insulator, conductor and tie.
- Fit is resilient and provides superior performance under galloping and aeolian vibration.

General

Application	Top Tie
Color Code	Green
EU RoHS Indicator	No
Insulator Throat Neck Type	C, F, J Neck & Spool
Material	Aluminum Clad Steel
Product Category	Ties
Type	Formed Wire
UPC	096359053354

Dimensions

Dimensions	17.000 in x 1.321 in x 2.233 in
Height	2.233 in
Length	17 in
Weight	0.64 lb
Width	1.321 in

Conductor Related

Conductor Diameter - Maximum	0.664
Conductor Diameter - Minimum	0.585
Conductor Diameter Range	0.585 - 0.664
Conductor Type	ACSR, AAC and AAAC

Logistics

Carton Quantity	50
Pallet Quantity	1050

Product Assets

[Catalogs - Distribution Connectors](#)
[Sales Drawings - STT Drawing](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
FG-STT100-SPEC-EN | REV 6/2024