

# SUPER TOP TIE™ Formed Wire Top Tie

By FARGO  
Catalog # [STT110](#)

SUPER TOP TIE™ for 336.4 ACSR, 336.4 AAC and 336.4 AAAC



## Features

- SUPER TOP TIE™ ties are used for securing the conductor in the top groove of vertical-mounted C, F and J-Neck interchangeable headstyle insulators and many non-standard pin and post insulators (single- or double-support) or on \*ANSI 53-2 spool insulators (horizontal or vertical).
- Semiconductor-rubber pad and high-density polyethylene on loops protect against abrasion of insulator, conductor and tie.
- Fit is resilient and provides superior performance under galloping and aeolian vibration.

## Application

Top Tie

## General

Color Code	Brown
Insulator Throat Neck Type	C, F, J Neck & Spool
Material	Aluminum Clad Steel
Product Category	Ties
Type	Formed Wire
UPC	096359053361

## Dimensions

Dimensions	23.500 in x 1.321 in x 2.285 in
Height	2.285 in
Length	23.500 in
Weight	0.800 lb
Width	1.321 in

## Conductor Related

Conductor Diameter - Maximum	0.755
Conductor Diameter - Minimum	0.665
Conductor Diameter Range	0.665 - 0.755
Conductor Type	ACSR, AAC and AAAC

## Logistics

Carton Quantity	50
Pallet Quantity	1200

## Product Assets

[Catalogs - Distribution Connectors \(CA05127E\)](#)  
[Sales Drawings - STT Drawing](#)